

Datasheet

## RS Pro Stainless Steel Pan Head Machine Screws, M3 x 25mm

RS Stock No: **914-1490**



### Product Details

RS Pro machine screw measuring M3 x 25 mm, is made of A2 grade stainless steel. This pan head screw is fully threaded and it can be used in pre-tapped holes or can be used with conforming nuts and washers in through holes. The cross recess screw is designed to give you ease of assembly. It is suitable for light engineering, domestic appliances and electronics applications. This machine screw meets DIN 7985 standards.

### Features and Benefits

- Good corrosion resistance
- Recyclable
- Non-magnetic

**Specifications:**

Drive Type	Pozidriv
Finish	Plain
Head Shape	Pan
Material	Stainless Steel
Length	25 mm
Stainless Steel Type	304 (A2)
Thread Pitch	0.5
Thread Size (Metric)	M3
Head Diameter	5.3 to 5.6 mm
Head Height	2.26 to 2.4 mm
Recess Diameter	1.50 to 1.75 mm
Specification	DIN 7985