




JUBILEE® JUNIOR



These mini clips, also known as nut & bolt clips, are ideal for small bore hoses with relatively low pressures, where little clamping force is required. Used in low pressure applications such as a fuel line.

Part No.	Adjustment mm	Band Width mm	Band Thickness mm	Recommended Torque Nm	Maximum Torque Nm	Maximum Pressure PSI	Part No.
NB0709MS	7-9	9.1	0.6	1.5	2.0	75	NB0709MS
NB0810MS	8-10	9.1	0.6	1.5	2.0	75	NB0810MS
NB0911MS	9-11	9.1	0.6	1.5	2.0	75	NB0911MS
NB1012MS	10-12	9.1	0.6	1.5	2.0	50	NB1012MS
NB1113MS	11-13	9.1	0.6	1.5	2.0	50	NB1113MS
NB1214MS	12-14	9.1	0.6	1.5	2.0	50	NB1214MS
NB1315MS	13-15	9.1	0.6	1.5	2.0	50	NB1315MS
NB1416MS	14-16	9.1	0.6	1.5	2.0	50	NB1416MS
NB1517MS	15-17	9.1	0.6	1.5	2.0	50	NB1517MS
NB1618MS	16-18	9.1	0.6	1.5	2.0	50	NB1618MS
NB1820MS	18-20	9.1	0.6	1.5	2.0	50	NB1820MS

Corrosion Resistance: 72 hours NSS Test

Fastening: 7mm A/F screw

Industry Recommendations:-

Quality Assurance:-



Mild Steel Zinc Plated

Part No.	Adjustment mm	Band Width mm	Band Thickness mm	Recommended Torque Nm	Maximum Torque Nm	Maximum Pressure PSI	Part No.
NB0709SS	7-9	9.1	0.6	1.5	2.0	75	NB0709SS
NB0810SS	8-10	9.1	0.6	1.5	2.0	75	NB0810SS
NB0911SS	9-11	9.1	0.6	1.5	2.0	75	NB0911SS
NB1012SS	10-12	9.1	0.6	1.5	2.0	50	NB1012SS
NB1113SS	11-13	9.1	0.6	1.5	2.0	50	NB1113SS
NB1214SS	12-14	9.1	0.6	1.5	2.0	50	NB1214SS
NB1315SS	13-15	9.1	0.6	1.5	2.0	50	NB1315SS
NB1416SS	14-16	9.1	0.6	1.5	2.0	50	NB1416SS

Corrosion Resistance: 1000 hours NSS Test

Fastening: 7mm A/F screw

Industry Recommendations:-

Quality Assurance:-



304 Stainless Steel