



PRODUCT-DETAILS

SAMHL20/25M

20MM SS-TPE COAT CONDUIT 25M - WH



General Information	
Extended Product Type:	SAMHL20/25M
Product ID:	7TCA296030R0440
EAN:	5020963801495
Catalog Description:	20MM SS-TPE COAT CONDUIT 25M - WH
Long Description:	Liquidtight. Anti-Microbial Conduit, Conduit Size - Metric 20 Millimeters / US Trade Size 1/2 Inch, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, IP40-IP69 Rating, Galvanised Steel Core, String Packed and Thermoplastic Jacket, Reel Length 25 Meters, White
Display Name:	SAMHL20/25M

Additional Information	
Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Suitable for indoor splash zone areas or food processing equipment

Ordering

EAN: 5020963801495

UPC: 786210212951

Dimensions

Outside Diameter: 21.1 mm

Technical

Number of Batteries: 0

Color: White

Material: Galvanised Steel Core, String Packed and Thermoplastic Jacket

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963801495

Package Level 1 Height: 8 in
203 mm

Package Level 1 Depth / Length: 16 in
406 mm

Package Level 1 Width: 16 in
406 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

