

Datasheet

## RS Pro 1 Phase 240VA Variac, 1 Output, 240V

RS Stock No: **890-2828**



### Product Details

RS Pro 1-phase 240 VA variac has heavy duty construction and enclosed style variable transformers for surface floor or wall mounting. The transformers are not designed to provide mains isolation but operates at mains voltage. All of the transformers need to be earthed using the earth studs provided. This variac has continuously variable AC output voltage with overvoltage tap for smooth linear output. It has single output with primary voltage rating of 240 V.

### Features and Benefits

- Single or three phase versions available in a range of current ratings
- Heavy duty construction
- High efficiency & excellent regulation
- No waveform distortion
- Silver plated commutator
- Overload capacity
- Negligible maintenance
- Trouble free long life

**Specifications:**

Construction	Encapsulated
Depth	110 mm
Diameter	86 mm
Dimensions	86 x 99 x 110 mm
Knob Rotation	Clockwise
Length	99 mm
Maximum Operating Frequency	60 Hz
Minimum Operating Frequency	50 Hz
Mounting Type	Surface
Number of Outputs	1
Number of Phases	1
Power Rating	240 VA
Primary Current Rating	1 A
Primary Voltage Rating	240 V ac
Protection Features	Overload Protection
Secondary Voltage Rating	0 to 240 V ac
Standards Met	RoHS Compliant
Termination Type	Termination Wire
Weight	1.6 kg