

# Eaton 12OEFMA45

Catalog Number: 12OEFMA45

Oil fuse-link, medium voltage, 45 A, AC 12 kV, BS2692 F01, 254 x 63.5 mm, back-up, BS, IEC, ESI, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage oil fuse	12OEFMA45
	EAN
	5027590432627
Product Length/Depth	Product Height
254 mm	63.5 mm
Product Width	Product Weight
63.5 mm	1900 g
Compliances	Certifications
BS 2692-1	IEC Rated
ESI 12-8	IEC60282-1

## Product specifications

### Type

fuse

### Application

protection of primary side transformer, and oil-filled fuse switch combination unit

### Amperage Rating

45 A

### Fuse indicator

with striker

### Fuse size

254 x 63.5 mm

### Breaking capacity

40 kA

### Installation technique

Oil

### Performance Cat According To IEC 60282-1

Back-up

### Product application

Primary side transformer protection

### Rated frequency - max

60 Hz

### Rated frequency - min

50 Hz

### Release characteristic

Other

### Standard

British Standard

### Utilization category

Other

### Voltage type

AC

### With striker

Yes

### Fuse diameter

63.5 mm

## Resources

### Technical service bulletins

[Datasheet - 12OEFMA45](#)

Class

Class back-up

Construction type

F01/BS 2692

Fuse shape

Cylindrical

Interrupt rating

40 kAIC

Construction size

63.5 x 254 mm

Voltage rating

12 kV

Fuse type

OEFM



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia