

## FEATURES

- **Polyacrylic Material:** Offers excellent chemical resistance and durability.
- **Maximum Operating Pressure of 2000 kPa:** Suitable for high-pressure applications.
- **Maximum Operating Temperature of 200 °C:** Performs well in high-temperature environments.
- **Rotary Speed of 10 m/s:** Supports high-speed operations without compromising sealing integrity.
- **14mm Section:** Provides optimal sealing performance for various applications.

## RS PRO 8m Polyacrylic Gland Packing, 14mm Section

RS Stock No: 606-576



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO gland packing is designed to provide reliable sealing solutions for industrial applications. Made from high-quality polyacrylic material, it is ideal for use in environments requiring robust sealing under high pressure and temperature conditions. The gland packing ensures efficient performance, reducing leakage and enhancing equipment longevity.

## General Specifications

Maximum Operating Pressure	2000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	10 m/s
Section	14 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Polyacrylic

## Operation Environment Specifications

Maximum Operating Temperature	200 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------