





Note3
Shield with copper malar Before over-malded.
456789;=<

BINDING



WIRE	PIN	TO	PIN	ASSY
RED CORE!)"	1			E0206
RED DRAID WIRE!) ,"	6			E0206
BLUE CORE!)"	2			E0206
Blue DRAID WIRE! * ,"	7			E0206
GREY CORE!)"	3			E0206
Grey DRAID WIRE! + ,"	8			E0206
NC 4				
BLACK!%"	5			E0206
NC 9				
BLACK!%"	10			E0206
RED !)"	11			E0206
WHITE!&"	12			E0206
BROWN!/"	13			E0206
YELLOW!0&"	14			E0206
NC 15				
SHELL		BRAIN		(SCR)E0206

P/N	Length
VGA-FRL-5M	5M±100MM
VGA-FRL-10M	10M±200MM
VGA-FRL-15M	15M±200MM
VGA-FRL-20M	20M±200MM

REV	DESCRIPTION	BY	DATE
B	BC LOGO	KANG	2009.10.29

6			TOLERANCES .XXX .025mm .XX .100mm .X .250mm Wire Length 0-100 5mm 101-300 10mm 301-500 15mm 501-<1000 20mm 1000-<2000 50mm 2000+ 100mm	TITLE: VGA CABLE					
5	E0206 >*&-?@A	12PCS		SHEET	FREE	UNIT	DRAWN	Auditing	APPROVED
4	M3 screw with % pvc	2PCS							
3	MOULD IN 55P % PVC	1PCS							
2	DB15 MALE ! INNER COLOR IS BLUE"	1PCS							
1	UL2919 28AWG! 3+5" VGA CABLE 17612 DD3 8.0MM JACKET BEIGE GREY PVC								
ITEM	DESCRIPTION	QTY	1 OF 1		MM	WU	WU	JACKY	