



**Part Number :** [191410052](#)  
**Product Description :** Krimptite Spade Tongue Terminal for 16-14 AWG Wire  
**Series Number :** 19141  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** BB-107-06



---

## Documents & Resources

### Drawings

[191410052\\_sd.pdf](#)


### Specifications

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Ring and Spade Terminals
Series	19141
Description	Krimptite Spade Tongue Terminal for 16-14 AWG Wire
Keyword	Spade Terminal, Spade Terminals
Product Name	Krimptite
Style	Spade
Type	Spade Connector, Metric Spade Connector
UPC	800755086461

#### Agency

CSA	LR18689
UL	E32244

#### Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.520/g
Packaging Type	Bag
Stud Size	5-6 (M3-3.5)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm <sup>2</sup>	1.30-2.00

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

---

This document was generated on Sep 24, 2025