

KERN HED 100

Shore hardness tester with extensive functionality

KERN

Category

| | |
|------------------|-------------------------------|
| Brand | Sauter |
| Product category | Hardness testing |
| Product group | Digital Shore hardness tester |
| Product family | HE |

Measuring System

| | |
|----------------------------------|---------|
| Measuring range Shore | 100 |
| Readability hardness [d] (Shore) | 0,1 |
| Measuring probe diameter | 18 mm |
| Test force Hardness measurement | 50 N |
| Test object thickness [Min] | 6 mm |
| Hardness scales | Shore D |
| Leeb Hardness Tester sensor type | D |
| Units | HD |
| Tolerance (% of [Max]) | 1% |

Display

| | |
|---------------------|----------|
| Display type | LCD |
| Display screen size | 32×21 mm |

Construction

| | |
|---------------------------|--------------|
| Dimension (W×D×H) | 153×50×29 mm |
| Dimension housing (W×D×H) | 153×50×29 mm |
| Material housing | plastic |

Functions

| | |
|------------------------|---|
| Function for averaging | ✓ |
| Limit-setting function | ✓ |
| Hold function | ✓ |
| Peak function | ✓ |

| | |
|--|-------|
| Memory function | ✓ |
| Memory - number of results | 500 |
| Statistic function | ✓ |
| Auto-off interval(s) in battery mode/rechargeable battery mode | 2 min |

Interface

| | |
|------------|------------|
| Interfaces | USB-Device |
|------------|------------|

Power Supply

| | |
|---|---------------------------|
| Supplied power supply | Accu & Power supply |
| Plug-in power supply type | Power adapter |
| Plug-in power supply / adapter for countries - included with the delivery | EURO |
| Input voltage power supply / power [Max] | 100 V - 240 V, 50 / 60 Hz |
| Input voltage device / power [Max] | 5 V 1000 mA |
| Battery / accumulator type | NiMH |
| Battery connection | Connector pin |
| Battery operating time - backlight off | 20 h |
| Battery operating time | 20 h |
| Battery voltage | 3,6 V |
| Rechargeable battery operating time - backlight on | 20 h |
| Rechargeable battery operating time - backlight off | 20 h |
| Rechargeable battery charging time | 3 h |

Approval

| | |
|---------|---|
| CE mark | ✓ |
|---------|---|

Packing & Shipping

| | |
|------------------------------|----------------|
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 295×165×115 mm |
| Net weight | 0,17 kg |
| Shipping method | Parcel service |
| Net weight approx. | 0,20 kg |
| Gross weight approx. | 0,80 kg |
| Shipping weight | 1,1 kg |

KERN HED 100



Shore hardness tester with extensive functionality

Pictograms

STANDARD

