

AlphaTec™

87-224

Heavyweight glove with reliable protection against a very wide range of chemicals

Previously known as: Chemi-Pro

Two-tone double-dipped work gloves, with a combination of neoprene and natural rubber



- **Specialized protection:** AlphaTec® 87-224 industrial gloves are two-toned and double-dipped, blending neoprene and natural rubber to offer personal protection against various chemicals
- **Enhanced defenses:** Thanks to their mediumweight thickness of 0.68mm/27 mil, they also provide a robust barrier against mechanical hazards
- **Elevated comfort:** Designed with 100% cotton flock lining, these sturdy work gloves absorb wearers' sweat, for greater comfort with sustained use
- **Strengthened grip:** These AlphaTec® safety gloves also feature a honeycomb pattern finish, boosting grip on wet and dry surfaces

Industries

- Automotive Aftermarket
- Machinery and Equipment
- Infrastructure Maintenance
- Janitorial / Sanitation
- Chemical
- Utilities
- Warehousing

Applications

- Maintenance of plant and heavy equipment
- Laboratory maintenance and clean up
- Janitorial use
- Chemical Handling

AlphaTec™

87-224

Heavyweight glove with reliable protection against a very wide range of chemicals

Previously known as: Chemi-Pro

Key Features

- **Neoprene and natural rubber blend:** Enhanced chemical resistance
- **0.68mm/27 mil thickness:** Greater mechanical protection
- **100% cotton flock lining:** Sweat absorption, for better comfort



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZ E	Length (MM/INC HES)	COLOR	PACKAGE
AlphaTec® 87-224	Liner Material: Cotton Flocking Coating Material: Natural Rubber Latex and Neoprene Blend	7, 8, 9, 10	325 / 12.8	Blue and Yellow	<ul style="list-style-type: none">• 12 pairs per bag, 12 bags per carton• Vending Pack: 1 pair per inner bag, 6 inner bags per master bag, 24 master bags per carton (FOR NA / LAC ONLY)

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

The Ansell logo, featuring the word "Ansell" in a bold, blue, sans-serif font with a green swoosh underneath.