

# A-INL-M25-N-S - Counter nut



1411243

<https://www.phoenixcontact.com/gb/products/1411243>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M25 x 1.5, color: silver-colored



## Commercial data

Item number	1411243
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 688 (C-2-2019)
GTIN	4046356923743
Weight per piece (including packing)	8.662 g
Weight per piece (excluding packing)	8.412 g
Customs tariff number	74198090
Country of origin	DE

# A-INL-M25-N-S - Counter nut



1411243


<https://www.phoenixcontact.com/gb/products/1411243>

## Technical data

### Product properties

Product type	Flat nut
Thread type	M25

### Dimensions

Dimensional drawing	
Length	3.5 mm
Diameter	25 mm
Connecting thread diameter	25 mm
Wrench size, counter nut	30 mm
Hexagon angular dimension	33.5 mm
Thread type connection side	M25 x 1.5
Thread pitch	1.5 mm

### Material specifications

Material	Brass, nickel-plated
----------	----------------------

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-70 °C ... 220 °C

# A-INL-M25-N-S - Counter nut


1411243

<https://www.phoenixcontact.com/gb/products/1411243>



## Drawings

Dimensional drawing



# A-INL-M25-N-S - Counter nut



1411243

<https://www.phoenixcontact.com/gb/products/1411243>

## Classifications

### ECLASS

ECLASS-13.0	27140807
-------------	----------

### ETIM

ETIM 9.0	EC000879
----------	----------

### UNSPSC

UNSPSC 21.0	31161700
-------------	----------

# A-INL-M25-N-S - Counter nut



1411243

<https://www.phoenixcontact.com/gb/products/1411243>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5f381a2d-ba08-4ae2-9804-d417980ab00a

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)