
Subject: E-125 - Cassiopeia (<http://www.casio.com/personalpcs/product.cfm?section=19&pro>)

Personal PCs **E-125 Cassiopeia**



Technical Specs

- CPU: VR4122 (150MHz)
- OS: Microsoft® Windows® for Pocket PC
- Memory: ROM-16MB, RAM-32MB
- Display: LCD 240x320 dots, Hyper Amorphous Silicon TFT color liquid crystal, 6 color, touch-panel display
- Interfaces: Serial port -RS-232C, USB (Client), Card slot - CF Card Type II x 1, I - IrDA 1.2; communications speed: 115.2 Kbps maximum
- Sound: Input - Internal microphone (mono), Output - Internal speaker (mono), he jack (stereo)
- Power source: Main battery - approx. 8 hours (when repeatedly operated 1 min. displayed 10 min.) Battery backup - approx. 5 years (when main battery is recha after charge warning message)
- Operating Temperature: 0-40°C
- Size and Weight: 83.6 (W) x 131.2 (L) x 20.0 (H) mm/approx. 250g (including ba

Compatibility of future products with past or current products can not be assured

SUBJECT TO CHANGE