

Previously known as: Vantage®70-765



Cut



Heat



Heavy Duty

Advanced cut-resistant safety gloves, featuring premium leather for superior grip

- **Enhanced defenses:** These safety gloves feature an aramid fiber and reinforced thumb crotch, as well as seams relocated to the back of the fingers, to guard against minor injuries, sharp snags and punctures
- **Specialized protection:** Among the best leather work gloves available, the ActivArm® 70-765 is also capable of protecting hands from intermittent heat contact up to 100°C/200°F
- **Strengthened grip:** They ensure strong, secure grip in oily environments
- **Improved durability:** ActivArm® 70-765 leather-palm work gloves feature a 10-gauge, mediumweight cut-resistant yarn, ensuring long-lasting use
- **Optimized comfort:** ActivArm® 70-765 safety gloves are not only heat-resistant, but comfortable and plaited with colored polyester and cotton



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Handling rough machined metal parts
- Glass repair and replacement
- Seizing rough blocs and cylinders
- Handling materials with sharp or rough edges
- Press shop operations

Previously known as: Vantage®70-765

Key Features

- **Double-stitched with aramid fiber:** Enhanced protection
- **Mediumweight cut-resistant yarn:** High cut protection-to-weight ratio
- **Heat-resistant design:** Intermittent heat contact up to 100°C/200°F

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X43D

EN 407



X1XXXX



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 70-765	Finishing: Leather Palm Coating Material: Leather Liner Material: Acrylic, Nylon, Aramid Cuff Style: Knitwrist	10	8, 9, 10, 11	235-275 mm/ 9.25-10.82 inches	Grey	12 pairs/bag, 3 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699