

## Protective hose - WP-STEEL ZC 36 - 3240700

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Galvanized steel protective hose, 1 Pcs. / Pkt. = roll à 10 m

Image shows WP-STEEL ZC 10  
GY version



### Key commercial data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 737203
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	83071000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Inner diameter (f)	31.00 mm
Outside diameter	36.00 mm

#### Ambient conditions

Ambient temperature (operation)	-200 °C ... 220 °C
---------------------------------	--------------------

#### General

Color	silver
Type	Spirals
Components	Halogen-free
Material	Steel, galvanized
Bending radius, static	85.00 mm

# Protective hose - WP-STEEL ZC 36 - 3240700

## Classifications

### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001179
ETIM 5.0	EC001179

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

#### Approvals

VDE Zeichengenehmigung

---


#### Ex Approvals

---

Approvals submitted

---

### Approval details

VDE Zeichengenehmigung 
--

## Accessories

### Accessories

Corrugated pipe screw connection

## Protective hose - WP-STEEL ZC 36 - 3240700

### Accessories

Screw connection - WP-G BRASS IP40 PG29 - 3241042



Cable gland made from brass with Pg thread, IP40 protection

---

Screw connection - WP-G BRASS IP40 M32 - 3241049



Cable gland made from brass with metric thread, IP40 protection

---

Screw connection - WP-GT BRASS PG29 - 3241028



Cable gland made from brass with Pg thread, rotatable, IP40 protection

---

Screw connection - WP-GT BRASS M32 - 3241035



Cable gland made from brass with metric thread, rotatable, IP40 protection

---

### Mounting material

Hose clamp - WP-BASE HF 37 - 3240972



Hose clamps

---

## Protective hose - WP-STEEL ZC 36 - 3240700

### Accessories

Protective hose fixing bracket - WP-BASE A PG29 - 3241081



Fixing bracket for protective sleeves, fixed with two screws

---

### Protective cap

Cable protection end sleeve - WP-SC BRASS 36 - 3241070



End sleeves as cable protection, made of brass

---

---