

Selection Guide | Combination Wrenches Ratchet



3 MODELS OF RATCHET COMBINATION WRENCHES FOR THE ULTIMATE VERSATILITY IN ANY APPLICATION

RINGSTOP

Ratcheting Spanner Set with Gothru Sockets

- The Rlingstop Gothru system employs a patented ring within the box end to prevent the Spanner from slipping past the fastener.
- Extremely useful when working on long bolts, or in positions where it is inconvenient to use the other hand to keep the tool on the fastener.
- Unlike traditional stop features, the Ringstop can be pushed past the fastener head when necessary, for use with double nut, or bolt and nut configurations.
- The Gothru sockets match the head size of each spanner, allowing access to smaller working areas. Ideal for use with inset fasteners, fasteners in tight areas and long bolts.
- The Ringstop can also be used with socket and bit adaptors, increasing the versatility of the tool.

Short combination wrenches

Productivity & accessibility

Ultra-compact:

- 40% more compact than the standard ratchet combination wrench.

Hinged combination wrenches

Productivity & manoeuvrability

- Ultra-manoeuverable: overcomes the problems of tightening and loosening in applications where the operator must work "blind".
- The hinged head offers unique accessibility as more compact than the ratchet-joint-socket association.

Standard combination wrenches

Productivity & versatility

Ultra-versatile:

- Ring head: ratchet mechanism with 5° increment, with 15° angle.
- Open end oriented at 15°.





SCMT22203

10 Piece Stubby Geared Wrench Set - Metric

Barcode: 9311927222033

Metric Wrenches - Reversible

10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm

SCMT51154 Replacement Box Only

330 x 140 x 50mm



SCMT22403

7 Piece Stubby Geared Wrench Set - AF

Barcode: 9311927224037

AF Wrenches - Reversible

3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"

SCMT51154 Replacement Box Only

330 x 140 x 50mm

Reversible Geared Wrench Stubby - Metric

Part No.	Barcode	Size
SCMT22300*	9311927223009	8mm
SCMT22301*	9311927223016	9mm
SCMT22275	9311927222750	10mm
SCMT22376	9311927223764	11mm
SCMT22277	9311927222774	12mm
SCMT22278	9311927222781	13mm
SCMT22279	9311927222798	14mm
SCMT22380	9311927223801	15mm
SCMT22281	9311927222811	16mm
SCMT22382	9311927223825	17mm
SCMT22383	9311927223832	18mm
SCMT22384	9311927223849	19mm

*Available September 2014



Reversible Geared Wrench Stubby - AF

Part No.	Barcode	Size
SCMT22490*	9311927224907	5/16"
SCMT22469	9311927224693	3/8"
SCMT22470	9311927224709	7/16"
SCMT22471	9311927224716	1/2"
SCMT22472	9311927224723	9/16"
SCMT22473	9311927224730	5/8"
SCMT22474	9311927224747	11/16"
SCMT22475	9311927224754	3/4"

*Available September 2014





SCMT22202

10 Piece Geared Wrench Set - Metric

Barcode: 9311927222026

Metric Wrenches - Reversible

10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm

SCMT51154 Replacement Box Only

330 x 140 x 50mm



SCMT22402

7 Piece Geared Wrench Set - AF

Barcode: 9311927224020

AF Wrenches - Reversible

3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"

SCMT51154 Replacement Box Only

330 x 140 x 50mm



SCMT22291

6 Piece Geared Wrench Set - Metric

Barcode: 9311927222910

Metric Spanners

8, 10, 11, 12, 13, 14mm