



Type	17647 101 001	Features (Technical)
Designation	Work Flex Pocket Light	1x China cool white LED as flashlight & COB cool white LED for work light
Battery required	3x AAA battery	Press button (Spot/Area/Off)
LED	1x LMP LTG4AW cool white LED, 1x COB LED	Strong magnet on pocket clip for hands free
Luminous intensity	Spot: 110 lumens or 400 cd Area: 100 lumens or 40 cd	Pocket Clip
Run Time	Spot 12 h Area 6 h	IPX4 water resistant
Range	40 m (calculated distance at maximum luminous intensity with an illuminance of 0.25 lux)	1 m Drop test (with magnetic holder)
Material	ABS PC (Polycarbonate) TPR (Thermoplastic Rubber) (All contact parts made of bronze or nickel-plated steel)	Eye risk group I
Weight	61.9 g	10,000 Switch cycle life
Dimensions		
A	173.8 mm	
B	30.7 mm	
C	24 mm	

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries