



ENGLISH

Datasheet

RS Pro LED Floodlight

RS Stock No: 145-5895



This RS Pro LED Floodlight is ideal for industrial and commercial applications, designed with a unique, ultra thin design for a modern look. Available in standard or PIR version.



ENGLISH

Typical Properties

Wattage	30W
Beam Angle	120°
Lumen Output	2700lm
Lamp Type	LED
Voltage	85V – 265V
Colour Temperature	Daylight
CCT (K)	6000K
Operating Temperature	-40°C to +60°C
Lamp	LED chip
Lifetime hours	30,000
IP Rating	IP65
IK Rating	IK08