

MECCA PRO 1/4", 3/8" & 1/2" SOCKET & TOOL SET 98 PIECES

ITEM ID: TMX098

Get Organised™



The TengTools TMX098 MECCA PRO 98-piece socket and tool set is a comprehensive collection designed for professional maintenance, assembly, and repair applications. Built to DIN and ISO standards, the set includes a carefully selected range of 1/4", 3/8", and 1/2" drive tools. The 1/4" drive 6-point metric sockets cover sizes from 4 mm to 13 mm, the 3/8" drive 6-point sockets span 8 mm to 21 mm, and the 1/2" drive 12-point sockets range from 10 mm to 30 mm. The sockets have a satin finish and are made from corrosion resistant chrome vanadium. The set is equipped with two FRP ratchets with 45-teeth mechanisms in 3/8" and 1/2" drive sizes. A 1/4" gearless palm ratchet offers compact and efficient handling in confined spaces, while the 1/4" magnetic bit driver ensures reliable bit retention. To further enhance functionality, the set includes a range of extension bars: 75 mm for 1/4" and 3/8" drives, and 125 mm for 1/2" drive. Adaptors for drive size conversion—3/8"F to 1/4"M and 3/8"F to 1/2"M—alongside a 3/8" hex bit adaptor, expand the compatibility of the set with other tools and accessories. The tool selection also incorporates a range of metric combination spanners in sizes from 8 mm to 19 mm. A variety of 1/4" hex drive screwdriver bits is provided, including flat (0.8 × 4.0 mm to 1.4 × 7.0 mm), PH (PH0 to PH3), PZ (PZ1 to PZ3), TX (TX10 to TX40), tamper-proof TPX (TPX10 to TPX40), ROB (ROB1 and ROB2), and metric and AF hex bits (3 mm to 10 mm and 1/8" to 3/8"). These bits, combined with the magnetic bit driver and adaptors, allow for secure and efficient fastening across a broad range of applications. The set is housed in a robust, hard-wearing MECCA PRO case for efficient transport and storage.

MECCA PRO 1/4", 3/8" & 1/2" SOCKET & TOOL SET 98 PIECES

Get Organised™

ITEM ID: TMX098

- "MECCA PRO 1/4", 3/8" & 1/2" Socket & Tool Set 98 Pieces
- 1/2" Ratchet FRP 45 Teeth
- 3/8" Ratchet FRP 45 Teeth
- Combination Spanner Metric
- 8, 10, 11, 12, 13, 14, 15, 16, 17, 19
- 1/4" Flat Bits 25 mm
- 0.8×4.0, 0.8×5.5, 1.4×7.0
- 1/4" Hex Bits 25 mm
- 3, 4, 5, 6, 8, 10
- 1/4" Hex Bits 25 mm AF
- 1/8, 9/64, 5/32, 3/16, 7/32, 1/4
- 1/4" Hex Bits 25 mm AF Hex 3/8"
- 1/2" Extension Bar 125 mm
- 1/2" Socket 12 pt Metric
- 10, 12, 13, 15, 16, 17, 19, 24, 27, 30
- 1/4" Extension Bar 75 mm
- 1/4" Socket 6 pt Metric
- 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13
- 3/8" Extension Bar 75 mm
- Reducing Adaptor 3/8"F - 1/4"M
- Step Up Adaptor 3/8"F - 1/2"M
- 3/8" Bit Adaptor Hex bit coupler 1/4" Hex
- 3/8" Socket 6 pt Metric
- 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21
- 1/4" Magnetic Bits Driver 193 mm
- 1/4" PH Bits 25 mm
- PH0, PH1, PH2, PH3
- 1/4" Gearless Palm Ratchet
- 1/4" PZ Bits 25 mm
- PZ1, PZ2, PZ3
- 1/4" ROB Bits 25 mm
- 1, 2
- 1/4" TPX Bits 25 mm
- TPX10, TPX15, TPX20, TPX25, TPX27, TPX30, TPX40
- 1/4" TX Bits 25 mm
- TX10, TX15, TX20, TX25, TX27, TX30, TX40"