

Wet / dry vacuum cleaner

GAS 35 H AFC Professional

User benefits

- Optimal protection of the health of users
H-Class/HEPA-PTFE filter provides high performance filtration and efficient collection of hazardous dust (and/or toxic material)
- Long-lasting suction power for continuous work progress thanks to the automatic filter cleaning (AFC)
- Usability:
Power tool connection socket with off/on function for better user convenience.



Technical data

- Nominal power input 1.200 W
- Max. suction power 1.380 W
- Device size (L/W/H) 590 x 740 x 400 mm
- Gross container volume 35 l
- Container volume net 25 l
- Max. Negative pressure (at the blower) 225 mbar
- Max. Air flow (at the blower) 74 l/s
- Dust extraction class H
- Weight net / gross 18 kg / 18,6 kg

- Scope of delivery: GAS 35 H AFC, H-class/HEPA mainfilter, PE Disposable bags, Safety filter bag, Antistatic hose, Pipes, Antistatic tool adapter, Joint nozzle, Pipe bend, Floor nozzle
- Packing size (L/W/H): -
- Quantity on pallet/VPE: -
- Goods-ID: 85081900
- Picturenummer: 336604
- Country of manufacture: Italien
- First delivery: Januar 2021



Description	Order-Nr.	Baretool-Nr.	EAN-Code	UVP € exkl. MwSt.	36 MVS
GAS 35 H AFC Professional	06019C3600	3601JC3600	4059952564494	869,-	D