

Datasheet

RS Pro Work Light Tripod, Fluorescent Tube, 58 W, 110 V IP65

RS Stock No: **670-2727**



Product Details

RS Pro fluorescent tube with work light tripod, has a voltage rating of 110 V ac and power rating of 58 W. It supports 1 x T8 linear fluorescent lamp and is IP65 rated. The yellow tripod stand has PC construction with epoxy painted finish for corrosion-resistant and durability. It is perfect for outdoor/indoor use such as construction sites and maintenance areas.

Features and Benefits

- Corrosion and impact resist
- Ideal for outdoor/indoor use i.e. construction sites, maintenance areas etc
- PC, with epoxy painted tubular steel yellow tripod stand
- 110 V ac operation
- Emergency version is an inverter/battery backed
- 58 W single tube type with 3 hour battery operation



ENGLISH

Specifications:

Case Material	PC
EU Energy Efficiency Rating	A
Height	1.6 m
IP Rating	IP65
Lamp Size	T8
Lamp Type	Fluorescent Tube
Type	Tripod
Voltage Rating	110 V
Wattage	58 W