



### Main

Range	Resi9
Product or component type	Trunking body
Range compatibility	Opale enclosure Resi9 enclosure
Cabling installation system	Housing wall trunking
Number of 18 mm modules per row	18
Standards	NF EN 50085-2-1 NFC 15-100

### Complementary

Trunking material	Plastic
Fixing mode	By screw
Cover fixing	Stapled
Provided equipment	1 trunking body 5 clip
Fire resistance	750 °C conforming to EN/IEC 60695-2-11
IP degree of protection	IP40 conforming to EN/IEC 60529
IK degree of protection	IK08 conforming to IEC 62262 IK08 conforming to EN 50102
Height	2600 mm
Depth	64 mm
Width	357 mm
Colour tint	White (RAL 9003)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations