



Verkaufs-Nr.: Gehäuse Typ	A	B	C	D
37 002209	230	193.5	160	210
37 003209	380	193.5	310	210
37 005209	530	193.5	460	210
37 002215	250	193.5	180	210
37 003215	380	193.5	310	210
37 005215	530	193.5	460	210
37 003316	330	243.5	260	260
37 004316	430	243.5	360	260
37 004416	410	323.5	340	340
37 005316	530	243.5	460	260
37 006316	630	243.5	560	260
37 003421	330	323.5	260	340
37 004421	410	323.5	340	340
37 006421	630	323.5	560	340
37 101006	130	43.5	60	60
37 151006	180	43.5	110	60
37 151508	180	93.5	110	110
37 201006	230	43.3	160	60
37 202008	230	143.5	160	160
37 202012	230	143.5	160	160
37 301508	330	93.5	260	110
37 302008	330	143.5	260	160
37 302012	330	143.5	260	160
37 303012	330	243.5	260	260
37 303016	330	243.5	260	260
37 383816	410	323.5	340	340
37 401508	430	93.5	360	110
37 402012	430	143.5	360	160
37 403016	430	243.5	360	260
37 503016	530	243.5	460	260
37 504016	530	343.5	460	360
37 602012	630	143.5	560	160