







RECOMMEND MINIMUM MOUNTING PITCH



PANEL CUT OUT



PCB LAYOUT (CONNECTOR REAR VIEW)

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- SHIELD BOX LEGS
- CONNECTOR LOCATION PINS

RJXS8FP15VE

SERIES PREFIX
CONTACT LAYOUT (RJ45 STYLE)
GENDER
THERMOPLASTIC 2.5mm to 3.8mm WITH CAP
TRANSMISSION CLASS (CAT5e)
VERTICAL MOUNT (PCB THRU HOLE)
WITH EMI/RFI SHIELD



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER		Amphenol		Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201	
LINEAR	ANGULAR	MATERIAL:	DRN: J.W	DATE: 30/12/2024	TITLE: XLrnet, VERT, IP65, SHIELDED, W/CAP, PANEL THICKNESS 2.5-3.8		PART No:
X ±10	X° ±1	SEE COMPONENTS	CKD: P.M.	DATE: 30/12/2024			RJXS8FP15VE
X.X ±5	X°X' ±30'	DO NOT SCALE	APP'D: P.M.	DATE: 30/12/2024			REV
X.XX ±1	X°XX' ±15'	FINISH: SEE COMPONENTS	SCALE: NTS	SIZE: A3			1
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS		THIRD ANGLE PROJECTION		DRAWING No.		SHEET	
DIMENSIONS IN MILLIMETRES				55011540-300-1		2/2	