

PRODUCT-DETAILS

TY242M-2

CABLE TIE 40LB 8IN RED NYLON



General Information

Extended Product Type	TY242M-2
Product ID	7TAG009160R0005
EAN	5414363061908
Catalog Description	CABLE TIE 40LB 8IN RED NYLON
Long Description	Cable Tie, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 208mm (8.2 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack

Ordering

EAN	5414363061908
UPC	786210714684

Dimensions

Product Net Width	0.14 in 3.6 mm
Product Net Depth / Length	8.2 in 208 mm

Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 1 Width	12 in 305 mm
Package Level 1 Depth / Length	18 in 457 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	13.4 in 340 mm
Package Level 2 Height	9.5 in 241 mm
Package Level 2 Depth / Length	21 in 533 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Red
Effective Date	19710315
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000566
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY242M-2

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

