

RL-DVV40

Reaction arm L-form for DVV

Code	ETIM
2653184	EC011814
EAN	UNSPSC
4010886934326	27-11-27-20
Country of origin	eCl@ss
Germany	21-04-91-90
Customs tariff number	
84679900	



Article description

- Straight pattern
- With adjustable reaction square
- Made of light metal

Article information

Contents (Qty of pieces)	1	Height of flange ring [mm]	30 mm
Net weight [kg]	1,737 kg	Radius of flange ring [mm]	42 mm
Total length [mm]	230 mm	Height of locking handle [mm]	63 mm
Material	Light metal/steel forged	Outside diameter [mm].	88 mm
Version reaction arm	L-Form, straight	Width reaction arm outer [mm]	48 mm
Distance drive square - start reaction arm (min.)	86	Height square [mm]	37 mm
Distance drive square - end reaction arm (max)	234		