

### PW310 - PW3 Hi-Vis V-Neck Mesh Insert T-Shirt S/S

**Collection:** PW3

**Range:** High Visibility

**Shell Fabric:** 55% Cotton, 45% Polyester, Knit

**Outer Carton:** 48

#### Product information

Designed for maximum comfort and breathability, this Cotton Comfort t-shirt offers excellent freedom of movement due to its segmented HiVisTex Pro tape design. Lightweight, stylish and breathable, this t-shirt has ventilating mesh panel inserts which allow air to circulate.

#### PW3

Utilising premium fabrics, products are engineered for flexibility across a diverse range of industry and trade end uses and offer exceptional value.

#### High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

#### Standards

EN ISO 20471 Class 2

RIS 3279 TOM Issue 2 (Orange Only)

ANSI/ISEA 107 TYPE R CLASS 2



#### Features

- Moisture wicking fabric helping to keep the body cool and dry
- High cotton content for superior comfort
- Underarm cool flow mesh panel for ventilation
- Modern styling with V-neck
- Taped neck seam for extra comfort
- Side vents for added comfort
- Designed with a comfort fit
- Heat applied segmented reflective tape for added visibility
- 40+ UPF rated fabric to block 98% of UV rays
- Certified to EN ISO 20471 after 50x washes
- Complies with RIS 3279-TOM for rail industry (orange only)

## PW310 - PW3 Hi-Vis V-Neck Mesh Insert T-Shirt S/S

**Commodity Code: 6109100010**

### Test House

ITS Testing Services (UK) Ltd. (Intertek) (Notified Body No.: 0362)  
 Centre Court  
 LE19 1WD, UK  
 Cert No: ITASLNB21021169

ITS Testing Services (UK) Ltd. (Intertek) (Notified Body No.: 0362)  
 Centre Court  
 LE19 1WD, UK  
 Cert No: LECFI00385084

### Wash Care



### Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
PW310YBRS	Yellow/Black	55.0	36.0	34.0	0.2760	0.0673	5036108349807	15036108838469
PW310YBRM	Yellow/Black	55.0	36.0	34.0	0.2760	0.0673	5036108349791	15036108838452
PW310YBRL	Yellow/Black	55.0	36.0	34.0	0.2880	0.0673	5036108349784	15036108838445
PW310YBRXL	Yellow/Black	55.0	36.0	34.0	0.3000	0.0673	5036108349814	15036108838476
PW310YBRXXL	Yellow/Black	55.0	36.0	40.0	0.3240	0.0792	5036108349821	15036108838483
PW310YBRXXXL	Yellow/Black	55.0	36.0	40.0	0.3520	0.0792	5036108349838	15036108838490
PW310YBR4XL	Yellow/Black	55.0	36.0	40.0	0.3620	0.0792	5036108349777	15036108838438