



Oil



Light Duty

Highly durable liquid-repellent industrial gloves, delivering superb grip performance

- **Specialized protection:** HyFlex® 11-920 safety gloves feature RIPEL™ Liquid Repellence Technology, an impermeable layer preventing oils or lubricants from making contact with skin
- **Enhanced grip:** ANSELL GRIP™ Technology treatment on their palm-dipped nitrile coating offers excellent grip in oily environments
- **Elevated comfort:** These HyFlex® gloves' seamless knit design ensures an ergonomic fit, for optimized comfort, dexterity and productivity
- **Improved durability:** HyFlex® 11-920 light-duty gloves are made with multi-layered nitrile coating to maximize wear longevity, satisfying ANSI/ISEA 105-2024 ABRASION LEVEL 4 and EN ABRASION LEVEL 3 standards
- **Assured practicality:** Machine launderable by design, they prove very economical over time, with less frequent replacement costs



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Oil and gas

Applications

- Assembly & inspection of components
- Production line support & maintenance
- Seizing structural parts
- Fabricating metal parts, glass sheets
- Applying finish to materials, products

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-920

Light duty oil repellent, oil grip multi-purpose glove

Key Features

- **RIPEL[™] Liquid Repellence Technology:** Heightened skin protection
- **ANSELL GRIP[™] Technology:** Secure grip when handling oily parts
- **Seamless knit design:** Outstanding fit, comfort and dexterity

Technologies

 **ANSELL GRIP[™]**
Ansell Grip Technology

 **RIPEL[™]**
Liquid Repellence Technology

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3131A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex [®] 11-920	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Nylon Cuff Style: Knitwrist	15	6, 7, 8, 9, 10	208-270 mm/ 8.18-10.62 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell