

**ENTE :
BODY :****VDE****Simbolo :
Symbol :****Riconosciuto conforme alle norme :
In accordance to standards :**DIN IEC 255 Teil 1-00 / DIN VDE 0435 Teil 201/05.83
DIN VDE 0435 Teil 201 A1/05.90
DIN IEC 255 Teil 0-20 / DIN VDE 0435 Teil 120/10.81

TIPO TYPE	Corrente nominale Nominal current Tensione nominale Nominal voltage	Vita elettrica a pieno Carico in AC1 (cicli) Electrical life at AC1 rated load (cycles)	Portata motore Motor rating	Temperatura ambiente Ambient temperature	N. File
55.X2	10 A – 250 Vac	200.000	/	85 °C	6434-4940-1017
55.X3	10 A – 250 Vac	100.000	/	40 °C	6434-4940-1011
55.X4	5 A – 250 Vac	100.000	/	70 °C	6434-4940-1022

/ (dato non disponibile)
/ (not available data)