



REV	Description	Date
A00	First Issue	2015-MAY-20




Pin Assignment:

Pin No.	Signal	Pin No.	Signal
1	CS0	16	VDD
2	RST	17	VDD2
3	CD	18	VSS
4	WR0	19	VSS2
5	WR1	20	VB1+
6	D0	21	VB1+
7	D1	22	VB1-
8	D2	23	VB1-
9	D3	24	VB0-
10	D4	25	VB0-
11	D5	26	VB0+
12	D6	27	VB0+
13	D7	28	VLCD_OUT
14	BM0	29	VLCD_IN
15	BM1	30	NC



- SPECIFICATIONS:**
- 1) STN/+VE/YG/TRANSFLECTIVE MODE
 - 2) 1/65 DUTY, 1/9 BIAS, VOP=10V
 - 3) VIEWING ANGLE = 6 O'CLOCK
 - 4) OP. TEMP.= -20°C TO +70°C
ST. TEMP.= -30°C TO +80°C
 - 5) DRIVER: UC1601S, VDD=3.3V
 - 6) WITH RGB LED(OSRAM LTRB GFSF) BACKLIGHT,
 - i) RED: 4.0V@:24mA;
 - ii) GREEN: 4.0V@:24mA;
 - iii) BLUE: 4.0V@:24mA
 - 7) ROHS COMPLIANT



Description: **MECHANICAL SPECIFICATIONS**

Scale: _____

Sheet : 1 of 1

Unspecified Tol. ±0.3 Unit mm

Approvals _____ Date _____

Draw: _____

Check: _____

Approve: _____

TRI-T COMPANY LIMITED

Project Number: CI064-4021-24

Item Number: _____

Do Not Scale This Drawing

Projection: