

Features

- 30 inch Drum Fan
- 3 speed fan and Rotary Switch
- Air flow options Maximum and 258.3m³/min
- Energy saving motor
- Quiet operation
- Aluminum blade
- Portable and Castor design allow the unit easy moved and positioned between locations
- Adjustable tilt fan head
- With handle design easy to move
- For indoor use only

RS PRO Industrial High Velocity 3 Speeds 30", Drum Fan, Type G British 3 pin

RS Stock No.: 0735031



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Buy this product from <https://uk.rs-online.com/>

RS PRO Industrial High Velocity 3 Speeds 30" Drum Fan

RS PRO 30-inch Industrial High Velocity Drum Fan delivers exceptional airflow performance for demanding environments. With a robust steel construction and 3-speeds operation, it efficiently circulates large volumes of air. The adjustable tilt fan head design, built-in handle and castors allow easy positioning and control. It is ideal for industrial, commercial and on-site use.

FEATURES & BENEFITS

- Powerful three-speed motor for high airflow output
- Moves up to 258.3m³ per minute for effective ventilation
- Heavy-duty steel casing guard and frame for durability
- Fully guarded blades for safe operation
- Adjustable tilt fan head, handle and castors for easy manoeuvrability
- Come with a 2.45m cable
- Suitable for workshops warehouse agricultural and construction sites

General Specifications

Air Flow	145 / 193.7 / 258.3m ³ /min
Blade Span	750 mm
Fan Type	Floor
Number of Speeds	3
Plug Type	Type G – British 3-pin
Supply Voltage	230V
Special Features	Durable ball-bearing motor

Electrical Specifications

Maximum Power Input	280W
Maximum Speed	1360rpm
Number of Blades	3
Number of Wheels	2
Overall Height	990mm
Overall Width	1005mm
Depth	400mm
Weight	22.4kg

Approvals

Declarations	REACH DoC
Certificate	CE
Standards Met	EN 60335-1:2012 + A11:2014 + A13:2017 + A1:2019 + A2:2019 + A14:2019 + A15:2021 + A16:2023

Similar Products

Stock No.	Brand	Product Name	Size	Air Flow	No of Speed
179-2262	RS PRO	Floor Fan	18-inch	70/80/100 m ³ /min	3

