

FEATURES

- Stainless steel bracket simply fitted to connector
- Easy jab-in connection, just push in wire & tighten screw
- Miniature connector size
- JIS colour coded
- Japanese Industrial Standards (**JIS**) are the standards used for industrial activities in Japan.

RS PRO Miniature Quick Wire Panel Mount Thermocouple Connector with Stainless Steel Bracket JM-K-SSPFQ Type K JIS

RS Stock No.: 771-8893



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Stainless steel bracket simply fitted to connector. Fully enclosed terminals with cable port seal

General Specifications

General Description	Easy jab-in connection, just push in wire & tighten screw
----------------------------	---

Specifications

Thermocouple Type	K JIS
Connector Type	Quick Wire Socket with Stainless Steel Bracket
Connector Size	Miniature
Colour	Blue
Max. Temperature	220°C
+Positive Contact	Nickel Chromium
-Negative Contact	Nickel Alloy

Approvals


RoHS Compliant	Yes
Standards Met	BS EN 50212:1997. RoHS

Thermocouple Connectors Product Guide

A comprehensive family of miniature and standard Thermocouple Connectors, accessories, panels, terminal and barrier blocks. Available in IEC, ANSI & JIS colour specifications.

[Click below to view:](#)

[RS Pro Thermocouple Connector Selection Guide](#)



**Miniature Socket -
Quick Wire with stainless steel mounting bracket**
(dimensions in mm)

RS Components is a leading provider for Automation and Control Gear, below is a selection of best selling products:

rspro.com  Temperature. It matters	Calibration Whether it's existing equipment or a new purchase, you need to have confidence in the accuracy of your measurements. That's where our calibration service can help. Purchase new products with confidence. A certificated calibrated sensor straight out of the box, ready to use. Best Sellers ANSI SYSCAL Type K Mineral Insulated Thermocouple RS 181-7296 IEC SYSCAL Type K Mineral Insulated Thermocouple RS 181-7288 IEC SYSCAL Type J Mineral Insulated Thermocouple RS 181-7305 RTD Detectors Wire-wound type provides greater accuracy and stability but are vulnerable to shock. Flat film type are resistant to shock and have quicker thermal response times. Various lengths and diameters available, in class A, B and 1/10th Din. Best Sellers PT1000 Thin Film Detector RS 362-9907 Allied 70643582 PT100 Wire Wound Detector RS 611-7839 Allied 70646151 PT100 Wire Wound Detector RS 362-9799 Allied 70643577
Exposed Junction Thermocouples Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications. 1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours. Best Sellers ANSI Type K Exposed Junction RS 814-0134 Allied 70656459 ANSI Type K High Temp Exposed Junction RS 131-4749 Allied 71080908 IEC Type K Exposed Junction RS 363-0250 Allied 70643600	Fabricated and Specialist Thermocouples Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available. Best Sellers Magnet Thermocouple RS 762-1115 Allied 70651739 Heavy Duty Thermocouple RS 762-1128 Allied 70651743 Rubber Patch Thermocouple RS 290-5036 Allied 70642886
Thermocouple & PRT Cable Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC & Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m. Best Sellers IEC PVC Insulated Flat Pair RS 219-4573 Allied 70641630 ANSI PFA Insulated Twin Twisted RS 814-0030 Allied 70656106 IEC Glassfibre Insulated Flat Pair RS 236-3836 Allied 70641730	Thermocouple Connectors Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available. Best Sellers IEC Thermocouple Plug RS 455-9764 Allied 70644391 ANSI Thermocouple Socket RS 769-1127 Allied 70652125 IEC Thermocouple PCB Socket RS 381-7570 Allied 70643749

RS Components is a leading provider for Automation and Control Gear, below is a selection of best selling products:

 Mineral Insulated Thermocouples Available in various calibration types with a variety of terminations. These include; Thermocouple plugs, Terminal heads and Thermocouple cable	Best Sellers  IEC Thermocouple with PTFE Cable RS 397-1236 Allied 70643843 IEC Thermocouple with Mini Plug RS 397-1488 Allied 70643863 ANSI Thermocouple with PFA Cable RS 847-1019 Allied 70658112	NEW PRODUCTS RS PRO, the own brand of RS Components, offers an unbeatable range of products across all industries with quality you can trust. New products are constantly added to improve the offering of our product range.	NEW PRODUCTS  Brake Pad Temp Sensor RS 200-0601 Allied 72173869 RTD Temp Sensor Hirschmann Style RS 200-0594 Allied 72173862 Washer Thermocouple RS 200-0616 Allied 72173882
 Sensors with Industrial Terminal Heads Industrial sensors housed in a stainless steel sheath and terminal head protection to IP67. Available as a thermocouple or Pt100.	Best Sellers  Type K 300mm Long RS 787-7829 Allied 70653306 Type K 200mm Long RS 787-7816 Allied 70653303 Type K 100mm Long RS 787-7804 Allied 70653235	www.rspro.com  www.alliedelec.com	
 L60 Fine Wire Thermocouple Welder The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.	Best Sellers  L60 Fine Wire Thermocouple Welder RS 363-0351 Allied 70825788 		