

STE-END-Q





Ordering information

Туре	Part no.
STE-END-Q	6021156

Other models and accessories → www.sick.com/

Detailed technical data


Technical specifications

Accessory group		Plug connectors and cables
Accessory family		Other connectors and cables
Connection type head A		Male connector, M12, 4-pin, straight, B-coded
Signal type		PROFIBUS DP
Special feature		Terminal resistor
Ambient operating temperature		
	Head	-40 °C +85 °C

Classifications

ECI@ss 5.0	27279201
ECI@ss 5.1.4	27279201
ECI@ss 6.0	27279201
ECI@ss 6.2	27279201
ECI@ss 7.0	27279201
ECI@ss 8.0	27279201
ECI@ss 8.1	27279201
ECI@ss 9.0	27440190
ECI@ss 10.0	27440190
ECI@ss 11.0	27440190
ETIM 5.0	EC002062
ETIM 6.0	EC002062
ETIM 7.0	EC002062
UNSPSC 16.0901	31163032

Dimensional drawing (Dimensions in mm (inch))



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

