



### Pneumatic Tensioning Tool with Plastic Housing

#### MK7P up to 4.8 mm strap width

The MK7P pneumatic bundling tool sets a new benchmark for the rational application of ties in the industrial production process. Improved compressed air supply moves the tensioning piston faster than in comparable tools.

#### Features and benefits

- Pneumatic tensioning tool
- Light glass-fibre-reinforced housing
- For cable ties up to 4.8 mm width
- For consistent tensioning and automatically flush cutting
- Infinitely adjustable tension force
- High application speed



MK7P.



The easy to use quick-set-knob.

<b>Air Supply</b>	Non oiled / oiled
<b>Air Pressure (min.)</b>	3 Bar
<b>Air Pressure (max.)</b>	6 Bar
<b>Hose Internal Diameter</b>	4.0 mm
<b>L x H x W</b>	approx. 220 x 170 x 40 mm



TYPE	Strap Width max.	Strap Thickness max.	Weight	Article-No.
MK7P	4.8	1.5	0.448 kg	110-07100
SP MK3PNSP2 air hose 3 meters	-	-	0.139 kg	110-30002
SP MK7P replacement blade	-	-	0.01 kg	110-07111
SP lock cap tensioning knob	-	-	0.011 kg	110-07200

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.