

zcy39

limit switch lever ZCY - thermoplastic roller lever Ø50 mm



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKD XCKP XCKT
Associated head	ZCE01 ZCE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic (roller diameter 50 mm)
Tracks	No track
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0851 - Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Available

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.