

Datasheet

Cordless Drill Driver

RS Stock number [394-027](#)



Features

- Torque, max. (hard/soft) 30 / 13 Nm
- No-load speed (1st gear / 2nd gear) 0 – 350 / 1.300 rpm
- Chuck capacity, min./max. 1 / 10 mm
- Battery voltage 10,8 V
- Weight incl. battery 0,95 kg
- Torque settings 20+1
- Length 169,0 mm
- Drilling diameter
- Max. drilling diameter in wood 19 mm
- Max. drilling diameter in steel 10 mm
- Screw diameter
- Max. screw diameter 7 mm