



ENGLISH

Datasheet

## RS Pro Straight Cable Mount F Connector, Plug, Crimp Termination, 0 to 1GHz, RG59

RS Stock No: **546-2734**



### Product Details

RS Pro panel mount connector jack is suitable for operating frequencies ranging from 0 - 1 GHz. It is compatible with RG59 cable and offers crimp termination. The copper contact ensures superior connectivity.

### Features and Benefits

- Nickel plated brass bodies with Delrin insulation
- Frequency range dc to 1 GHz
- In screw on and crimp versions
- Screw-on type have an internal thread which bites into braid

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Cable Type	RG59
Contact Material	Copper
Gender	Male
Mounting Type	Cable Mount
Operating Frequency	0 to 1 GHz
Termination Method	Crimp
Dimensions	16.2 x 11 mm
Operating Temperature Range	-65 to +165°C