

Amazon Monitron Data Sheets

Technical Details

AMAZON MONITRON SENSOR



Technical Details	-20 +80°C / -4 +176°F
Dimensions	52.8 x 43.0 x 24.9 mm / 2.08 x 1.69 x 0.98 inch
Weight	54 grams
IP Rating	IP65
Mounting method	Instant adhesive / Epoxy
Wireless protocol	Bluetooth Low Energy 5
Vibration sensor	3-axis MEMS accelerometer, range +/-16g, frequency response up to 6kHz, sampling frequency 26.7kHz
Power	Lithium Metal Non-Rechargeable Batteries
Battery life	Estimated 3 years
Default data capture frequency	once an hour

ADDITIONAL INFORMATION

Warranty and Terms	Three years limited warranty . Use the Amazon Monitron Starter Kit is subject to the terms found here .
California residents	Click here for Proposition 65 warning.

Technical Details

MONITRON GATEWAY



Operating temperature	0 - 40°C / 32 - 104°F
Dimensions	90 x 78 x 38 mm / 3.6 x 3.1 x 1.5 inch
Weight	95 grams
IP Rating	IP65
Internet connectivity	WiFi, 802.11b/g/n, ISM 2.4GHz only
Power	Power 5.0V - 2.0A DC, AC adapter included for USA, UK and EU countries (indoors only)

ADDITIONAL INFORMATION

Warranty and Terms	Three years limited warranty . Use the Amazon Monitron Starter Kit is subject to the terms found here .
California residents	Click here for Proposition 65 warning.