

## Datasheet

### **RS Pro Case, 225 x 599 x 439mm**

RS Stock No: **389-1663**



## **Product Details**

RS Pro case measuring 225 x 599 x 439 mm, is a tough lightweight instrument storage case. It comes with pick and pluck foam in the base and egg box style foam in the lid. Deep drawn aluminium cases offering security and protection for any electronic, electrical, sensitive or fragile equipment. It incorporates a strong black soft anodised frame with integral high impact keylocks. An inner rail provides the opportunity for mounting a panel securely within the case enabling test and measurement, environmental equipment to be located by cutting the panel holes as required.

## **Features and Benefits**

- Scratch resistant and dent resistant
- IP65 integral seal
- Recessed for protection
- Robust comfortable handle and lockable metal catches
- Supplied with two keys
- Optional pre-drilled aluminium panel can be supplied for panel mounted equipment to be fitted
- Lid depth of 50 mm on all sizes



ENGLISH

## Specifications:

Colour	Silver
Dividers	No
External Depth	439 mm
External Dimensions	225 x 599 x 439 mm
External Height	225 mm
External Width	599 mm
Foam	Yes
Internal Depth	412 mm
Internal Dimensions	200 x 571 x 412 mm
Internal Height	200 mm
Internal Width	571 mm
Lockable	Yes
Material Type	Plastic
Material	ABS
Watertight or Waterproof	No
Wheels	No

## Standard Sizes

Model Number	Panel Size (mm)	Dimensions (In Millimetres)						
		A	B	C	D	E	F	G
<b>389-1657</b>	386 x 274	225	155	70	300	412	150	50
<b>389-1663</b>	488 x 386	225	155	70	413	515	150	50
<b>389-1663</b>	572 x 412	225	155	70	439	599	150	50

