

Braided Wire

Features

- M6 to M6 Stud size
- Soft Tinned Copper
- Brazed seam
- CSA 10.05 mm²
- 24 x 20 x 0.2 mm

RS PRO M6 to M6 Copper Braided Wire 150mm

RS Stock No.: 489-210



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Soft Tinned Copper braided wire suitable for applications which require a strong and flexible braided connection. Typically used within automotive, aerospace and railways industries.

- *High flexibility braid for high vibration areas*
- *Brazed seam terminal construction*
- *Conforms to BS4109*

General Specifications

Size	24 x 20 x 0.2 mm
Conductor Material	Tinned Copper
Cross Sectional Area	10.05 mm ²
Length	150mm
Conductor Resistance	1762 Ω/km
Stud Size	M6
Cable Shape	Single Core

Approvals

Standards Met	BS EN 13602:2002, BS4109
---------------	--------------------------