



Pushing Performance
Since 1945

Han-Port single frame, plastic



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 000 0320
Specification	Han-Port single frame, plastic
HARTING eCatalogue	https://harting.com/39500000320

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Frames
Specification	Single
	Plastic version, PBT black
	Plastic cover, ABS metallic silver

Technical characteristics

Limiting temperature	-10 ... +60 °C
Storage temperature	-25 ... +60 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Specifications and approvals

UL / CSA	UL 508 NITW2.E472460
	CSA-C22.2 No. 14-95 NITW8.E472460

Commercial data

Packaging size	1
Net weight	87 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140154810
eCl@ss	27182810 Cover/infill panel/identification strip (electrical cabinet)
ETIM	EC002617
UNSPSC 24.0	39121321