



Digicheck 5 Voltage Tester

Technical Specifications

- Voltage Range: 5-690V AC/DC
- Voltage Indication: 4-Digit LCD Display & LED
- Input Resistance: 300 K Ohm
- Continuity Testing: 0-2 K Ohm (With LCD display and audible buzzer for continuity & voltage)
- Peak Current Resistance: 5 KV
- Frequency Range: 0-2000Hz
- Battery Type: 9V PP3
- Battery Capacity: 2000 Operations
- Enclosure: IP50
- Ambient Temperature: -10 - +50 Degrees Centigrade
- Tested And Approved In Accordance To VDE 61010 Part 1