

FEATURES

- Pozidriv head type for improved screwdriver grip
- Countersunk head for a flush finish
- A4 316 Marine Grade stainless steel
- Easily Cleanable
- Meets DIN 965 Standards

RS PRO, M3 Countersunk Head, 10mm Stainless Steel Pozidriv A4 316

RS Stock No.: 914-1945



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO a high-quality machine screw with a flat countersunk head for flush fitting and a versatile Pozidriv recess for a superior grip when tightening. This machine screw has a metric thread and is made from high quality A4 316 stainless steel which has excellent corrosion resistance. Grade 316 steel is also known as marine grade stainless steel due to its increased resistance to chloride corrosion making it ideal for use in marine applications.

General Specifications

Head Shape	Countersunk
Drive Type	Pozidriv
Applications	Swimming pools, Chemical plants, Boat deck fittings, Dairy equipment, Medical sterilising equipment, Sewerage treatment plants

Mechanical Specifications

Thread Size (Metric)	M3
Length Metric	10mm
Material	Stainless Steel
Finish	Plain
Stainless Steel Type	316 (A4)
Thread Pitch	0.5mm
Head Diameter	5.2mm to 5.5mm
Head Height	1.65mm
Recess Diameter	1.76mm to 2.01mm
Specification	DIN 965

