



Oil



Medium Duty

Three-quarter dipped nitrile-coated gloves, offering mechanical protection and a firm grip

- **Heightened durability:** Owing to their three-quarter dipped nitrile coating, EDGE[®] 40-400 industrial gloves can outwear the standard split leather alternatives and protect the fingers and knuckles against dirt, snags and oils
- **Enhanced ergonomics:** Contoured to the shape of the hand, these ergonomic gloves ensure improved movement and dexterity
- **Optimized comfort:** To ensure comfort and breathability, EDGE[®] 40-400 protective gloves are made of soft, sweat-absorbent cotton liner
- **Food handling compliance:** Owing to their FDA-compliant materials, these food gloves are ideal for food packaging



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Metalworking & assembly operations
- Feeding the press and removing spare parts from it
- Picking parts and accessories
- Press work
- Press shop operations
- Fabricating metal parts, glass sheets

Key Features

- **Three-quarter dipped nitrile coating:** For safety gloves with a firm grip
- **Ergonomic features:** Assured tactile sensitivity for intricate tasks
- **Cotton liner:** Breathable, lightweight and comfortable hand protection

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4121A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 40-400	Finishing: ¾ Coated Coating Material: Foam Nitrile Liner Material: Cotton Cuff Style: Knitwrist	N/A	7, 8, 8.5, 9, 10	273-289 mm/10.7-11.3 inches	Grey	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.