



### Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	LC1D09...D38 LC1DT20...DT40

### Complementary

Mounting location	Side
Mounting mode	By clips
Suppressor technology	RC circuit
Control circuit voltage	24...48 V AC <= 400 Hz
Maximum peak voltage	3 Uc
Product weight	0.012 kg

### Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.