

STUBBY COMBINATION SPANNER METRIC 14MM



- Ideal for use in confined spaces
- Off set at 15° for easier use on flat surfaces
- TengTools hip grip design for contact with the flat side of the fastening
- Chrome vanadium satin finish
- Designed and manufactured to DIN3113A

Stubby Combination Spanner 14mm

General information

Country of origin: Taiwan
Barcode: 5020385041868
Tarriff code Europe: 8204110000
ECCN US: EAR99
ETIM: EC002176
UNSPSC: 27111713

Dimensions

Net weight (g): 66
Length: 115 mm

Attributes

Product type: Combination Spanners
Material: CrV
Certificates: N/A
Size: 14 mm
Tethering facility: No
Spanner type: Stubby
Unit of measurement: Metric
Jaw diameter: 28.9
Jaw height (mm): 7.4
Offset angle jaw (°): 15
Ring diameter (mm): 21.8
Ring height (mm): 9.1
Offset angle ring (°): 15

Features



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden