

NELCO CONTACT AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se





VPC 200

E1626659

CUTTING TOOL-RIGID PIPES, PREWIRED CONDUITS, CABLE OUTER SHEAR MAX=22mm, INNER SHEAR MAX=10mm

Perfect for cutting rigid, corrugated and pre-wired conduits. Two blade cutting tool, outer shear is used for cutting plastic parts and the inner shar for the cables. It is easy, gives perfect result and saves time.

Cutting capacity (diameter):Pipes: 22 mmCable: t.ex. 5 x 2.5 mm² eller 25 mm².Length: 205 mm

Product Properties:

Suitable for stainless steel	No
Suitable for aluminium	No
Suitable for copper	Yes
Suitable for steel	No
Suitable for cast iron pipe	No
Suitable for plastic	Yes
Suitable for multi-layer composite pipes	Yes
With inner tube deburrer	No
With quick adjustment	Yes
Telescopic	No
Number of cutting wheels	0-0 .

Dimensions:

Unit	pcs
Tube diameter	0-22 mm
Length	205 mm
MOQ	1.

Approvals:

Compliance:

RoHS RoHS 3 (2015/863)

Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (223 Subs. Jan 2022)

Other information:

ETIM-Class	EC000148 - Pipe cutter
ETIM-Release	8.0
Product Group	Pipe, Conduit and Hose Tools
Search Description	CCTOOLS, ENR202009
Alternative SKU	VPC200

Logistic information:

Barcode	733117611070
E-no	E1626659
Country of origin	JP
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	VPC 200
Taric code	82032000
Unit	pcs
MOQ	1.