

Main

Range	PrismaSeT Active
Range of product	PrismaSeT G Active
Product or component type	Canopy
Accessory / separate part category	Enclosure accessory
Range compatibility	PrismaSeT PrismaSeT G Active enclosure
IP degree of protection	IP41

Complementary

Installation description	2 floor-standing enclosure - width 600 + 600 mm 2 wall-mounted enclosure - width 600 + 600 mm
Quantity per set	Set of 1
Height	45 mm
Width	1200 mm
Depth	280 mm
Net weight	5.14 kg
Surface finish	Matt Textured
Material	Treated sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.