



verso mobile storage bench with 1 drawer-door cabinet / 1 drawer-door cabinet. Featuring a robust, steel channel framework with integrated storage units 125mm diameter castors and a 30mm multiplex wood worktop. Delivered assembled. Equivalent cabinet - WxDxH:525/525x550x600mm. Drawer configuration: 2x 125mm with 100% extension slides (75kg U.D.L.) with two, reinforced 350 mm high. Finished in durable powder coat paint in RAL 7035 light grey / RAL 3004 crimson red. WxDxH: 1250x600x830mm.

Breite [mm]: 1250
Tiefe [mm]: 600
Höhe [mm]: 830
Bruttogewicht [kg]: 88.89
EAN-Code: 5039350102756
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Crimson red
Main RAL colour	RAL 3004
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	2
Drawer load capacity [kg]	75
Drawer height 1 [mm]	125
Drawer height 2 [mm]	125

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Beech Multiplex
Door type	Plain
Door height 1 [mm]	350