

40Vmax Pole Hedge Trimmer XGT®

UN001G

600 mm

Model UN001G is a cordless pole hedge trimmer powered by a 40Vmax XGT Li-Ion battery.

This model is capable of cutting thick branches with high power, comparable to engine models. It is also the lightest in its class, offering excellent usability. Feature and benefits: Reverse function to clear jams, 3 speeds, Electric brake, 2 grips, Adjustable blade angle, Constant speed control, Foldable storage.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2000 / 3000 / 4000 min ⁻¹
No load speed	1000 / 1500 / 2000 min ⁻¹
Length Of Blade	600 mm
Max blade opening	25 mm
Angle range vertical	115 °
Continuous Use XGT® 40V Max / 4.0 Ah	65 min
Brushless Motor	✓
Sound Power Level (L _{WA})	93 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	4,9 / 3,5 m/s ²

User benefits

- Reverse rotation system frees the blade when it is jammed by thick branches
- Electric brake for maximum productivity and increased operator safety
- 3-speed options (Low / Medium / High) allows the operator to match speed to application

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing