










Connecting cable Length 1.0 m, round, for connection of basic unit, current measuring module, current/voltage measuring module, operator panel or extension modules via the system interface



General technical data	
Product brand name	SIRIUS
Product designation	connecting cable
Design of the product	Length 1.0 m, round
Ambient temperature	
• during storage	-40 ... +80 °C
• during operation	-25 ... +60 °C
• during transport	-40 ... +80 °C

Certificates/ approvals

General Product Approval	EMC	Declaration of Conformity	Test Certificates	Shipping Approval
 UL		 RCM	 EG-Konf.	Type Test Certificates/Test Report  ABS

Shipping Approval	other			
 LRS	 PRS	 RMRS	Confirmation	PROFINET-Certification  Profibus

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7937-0BA00-0>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7937-0BA00-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7937-0BA00-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7937-0BA00-0&lang=en

